

1412080
<https://www.phoenixcontact.com/gb/products/1412080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M12, Front mounting

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Easy device integration, thanks to mechanical port screw connections with press-in contour
- Efficient PCB assembly: two-piece connectors for SMT soldering

Commercial data

Item number	1412080
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ABQBCD
Product key	ABQBCD
GTIN	4046356992985
Weight per piece (including packing)	7.58 g
Weight per piece (excluding packing)	7.5 g
Customs tariff number	74153300
Country of origin	DE

SACC-FP-M-M12/PRESS SMD - Housing screw connection



1412080

<https://www.phoenixcontact.com/gb/products/1412080>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Panel mounting base
Thread type	M12

Material specifications

Material	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated

Connector

Connection 1	
Head design	Pin
Head thread type	M12

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

Environmental and real-life conditions

Ambient conditions	
Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Mounting

Mounting type	Front mounting Press-in mounting
Assembly note	Press-in mounting

SACC-FP-M-M12/PRESS SMD - Housing screw connection



1412080
<https://www.phoenixcontact.com/gb/products/1412080>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

SACC-FP-M-M12/PRESS SMD - Housing screw connection



1412080

<https://www.phoenixcontact.com/gb/products/1412080>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk