

# 3.5mm Washer Thermocouple, Type J with 2m of Glassfibre stainless steel overbraid

Type J Thermocouple housed in a 3.5mm washer eyelet, Grounded tip for quick response.

Each washer thermocouple has 2m of glassfibre & stainless steel overbraid cable for added protection and mechanical strength.



Specification Table	
Sensor Type	Thermocouple housed in a washer eyelet
Thermocouple Type	J (Iron/Copper Nickel)
Thermocouple junction	Grounded
Tolerance class	2
Washer size	3.5mm clearance hole
Washer material	Tin plated copper
Cable type	Fibreglass insulated flat pair with stainless steel overbraid
Conductor wire size	7/0.2mm
Cable length	2 metres
Termination type	Tail wires with stripped ends
Colour code (+ Pos)	Black
Colour code (-Neg)	White
Max. Temperature	+350°C
Other	n/a
Standards met (colour code)	IEC 60584:3
Standards met (wire tolerance)	IEC 60584:1

Thermocouple Type	Washer Size	RS Order Code
J	3.5mm	2000605