



TECHNICAL DATA

OZZYJUICE® SW-3: TRUCK GRADE DEGREASING SOLUTION

A unique mixture of pH-neutral emulsifiers and surfactants containing no solvents. CRC SmartWasher® OzzyJuice® SW-3 Truck Grade Degreasing Solution is a water-based, pH neutral cleaning fluid that is used to effectively clean parts, removing grease and grime. It's a biodegradable cleaning fluid for use in the CRC SmartWasher® Parts Washing System.



FEATURES & BENEFITS:

- NSF A1 approved (161215)
- Bioremediating
- pH neutral
- Water based
- Non-hazardous, non-flammable
- Non-toxic, non-irritating
- Less expensive to use than solvent unit
- Reduces compliance

APPLICATIONS:

Parts cleaning in preventative maintenance & repair facilities, industrial manufacturing plants, automotive repair shops, metal fabricators.

DIRECTIONS:

Add as supplied to the SmartWasher® as needed. Light comes on when the Smartwasher is low on Ozzyjuice®, see Operating manual for further instructions. Do not store below 0°C. Dispose of contents and container in accordance with local, regional, national and EU regulations.

TYPICAL PRODUCT DATA

20 Litre Pail:	1032075
NSF A1:	161215
Appearance:	Slightly hazy liquid
Evaporation Rate:	Very slow
Flash Point:	None
pH:	7.0 - 8.0
Plastic Safe:	Yes
Specific Gravity:	1.0182
VOC %:	<0.1
Optimal Working Temp (°C):	40 - 46 °C

OZZYJUICE DEGREASING/ CLEANING SOLUTIONS

Crude Oil:	Excellent
Hydraulic Trans. Fluid:	Excellent
Motor Oil:	Excellent
Solder & Flux:	Good
Bearing Grease:	Excellent
Automotive Grease:	Excellent
Resin Products:	Excellent
Fifth Wheel Grease:	Excellent
Creosote:	Excellent
Impacted Grease:	Excellent
Animal Fat:	Excellent
Automotive Varnish:	Good
Burned-On Carbon:	Good
Cutting Oils:	Good
Ink/Toner:	Fair
Asphalt:	Good



Version Number: 2 Date of Issue: 28/04/2022 Date of Update: 29/10/2025

