

Model No. 8420EURD

4,50m long x 10mm diameter Python™ adjustable locking cable; black and yellow

Best Used For:


Fences


Grills & Lawnmowers


Residential Gates & Fences


Tools & Ladders

Security Level:



Basic to medium security:

Generally recommended for indoor general purpose

Overview & Features

Product Features

- Patented locking mechanism holds the cable tight at any position from 30cm to 4,5m for infinite locking positions
- Interchangeable cables for application flexibility
- 100% steel braided cable
- Weather tough and rust resistant lock body and cable
- Vinyl sleeve and lock body bumper prevents scratching
- Strap holds excess cable for compact storage

Product Details

The Master Lock No. 8420EURD Python™ Adjustable Locking Cable is 4,5m long and features 10mm diameter braided steel for maximum strength and flexibility. The protective vinyl coating protects against scratches. The integrated pin tumbler keyed locking mechanism provides superior pick resistance. The rust resistant lock and vinyl coated cable provide superior weather and scratch resistance. The Limited Lifetime Warranty provides peace of mind from a brand you can trust.

Product Specifications

Product Number	8420EURD
Cable/Chain Length	4,5m
Outside Diameter of Cable/Chain	10mm
Colour	Black/Yellow
Description	Keyed Different, Retail Carded Packaging
Master Carton Qty	4

Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu