

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC

Collection: Kaptiv

Upper: Breathable Fabric

Insole: Wire Lace System

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10



Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.

Base

Comfort is what has inspired Base Protection since its first day of activity. The company produces safety footwear, combining technology and functional requirements, to respond to professional and more demanding clients.

Standards

EN ISO 20345: 2011 S1P (HRO SRC)

Features

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

PORTWEST®



B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC

Commodity Code: 6404199000

Test House

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)
Via Alberto Riva Villasanta, 3
, Italy
Cert No: N° F-113-05202-22

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1004BKO36	Black/Orange	67.0	41.0	36.0	1.1700	0.0989	8054633495094	
B1004BKO37	Black/Orange	67.0	41.0	36.0	1.1790	0.0989	8054633495100	
B1004BKO38	Black/Orange	67.0	41.0	36.0	1.2020	0.0989	8054633495117	
B1004BKO39	Black/Orange	67.0	41.0	36.0	1.2530	0.0989	8054633493182	
B1004BKO40	Black/Orange	67.0	41.0	36.0	1.3400	0.0989	8054633493199	
B1004BKO41	Black/Orange	67.0	41.0	36.0	1.3600	0.0989	8054633493205	
B1004BKO42	Black/Orange	67.0	41.0	36.0	1.4400	0.0989	8054633493212	
B1004BKO43	Black/Orange	67.0	41.0	36.0	1.4700	0.0989	8054633493229	
B1004BKO44	Black/Orange	67.0	41.0	36.0	1.5300	0.0989	8054633493236	
B1004BKO45	Black/Orange	67.0	41.0	36.0	1.5800	0.0989	8054633493243	
B1004BKO46	Black/Orange	67.0	41.0	36.0	1.5350	0.0989	8054633493250	
B1004BKO47	Black/Orange	67.0	41.0	36.0	1.6200	0.0989	8054633493267	
B1004BKO48	Black/Orange	67.0	41.0	36.0	1.6290	0.0989	8054633493274	