



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:36 (UTC)



23024CDE4

Spherical Roller Bearings

Boundary Dimensions

d	120	mm	Bore diameter
D	180	mm	Outside diameter
B	46	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	395000	N	Basic dynamic load rating
C0r	525000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	3200	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	4500	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1800	min-1	Grease lubrication
Oil (Oil-bath)	2200	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	130	mm	Diameter of shaft abutment
da (max.)	134	mm	Diameter of shaft abutment
Da (min.)	163	mm	Diameter of housing abutment
Da (max.)	170	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.22	Constant
Y2	4.5	Axial load Factors
Y3	3	Axial load Factors
Y0	2.9	Axial load Factors

Mass

Mass approx.	4.11	kg	Mass approx.
--------------	------	----	--------------

