

Empty enclosure

GTi 3-t



GTi 3-t

Empty enclosure

CUSTOMIZABLE

Productnumber: 01000301

Dimensions: 320 x 440 x 179 mm

Empty Enclosure - Industrial Quality -, 3 x housing connectors (GGV)

with transparent cover



Technical Data

electrical characteristics

Protection type UL:	3R
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Type of protection:	IP65
Protection class:	II

Colours

Base unit colour:	grey
-------------------	------

Dimensions

Width:	320 mm
Length:	440 mm
Height:	179 mm

Dimensions

Inner height:	157 mm
---------------	--------

Material characteristics

suitable for exterior use:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Halogen free:	yes
Industry quality:	yes

mechanical properties

Type of fastening:	Surface mounted
Cover screw torque:	2.5 Nm
Stackable:	yes
Impact strength:	IK08

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

Accessories

[07251301 - GFS 13-m - Flange set](#)

[07335001 - GFW 30 - Weather protection cover](#)

[07345001 - GFW 40 - Weather protection cover](#)