

ESL 60X10 - Insert strip



0804287

<https://www.phoenixcontact.com/gb/products/0804287>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, CMS-P1-PLOTTER, perforated, mounting type: insert, Number of individual labels: 72, text field height: 10 mm, text field width: 60 mm



Your advantages

- ESL 60x10, white insert label, for marking the UBE/D (60x10) terminal strip marker carrier
- The material file can be downloaded under the PROJECT complete software under Downloads – “Software update – Marking”

Commercial data

Item number	0804287
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2114
Product key	BG2114
Catalog page	Page 543 (C-3-2019)
GTIN	4055626291642
Weight per piece (including packing)	14.223 g
Weight per piece (excluding packing)	9.99 g
Customs tariff number	39206219
Country of origin	DE

ESL 60X10 - Insert strip



0804287

<https://www.phoenixcontact.com/gb/products/0804287>

Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Terminal marking
--------------	------------------

Marking

Number of individual labels	72
Number of individual labels per row	3

Dimensions

Width	10 mm
Length	60 mm

Text field

Text field width	60 mm
Text field height	10 mm

Material specifications

Color	white (RAL 9010)
Material	Polyester foil
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
---------------	-------------------

ESL 60X10 - Insert strip



0804287

<https://www.phoenixcontact.com/gb/products/0804287>

Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

ESL 60X10 - Insert strip

0804287

<https://www.phoenixcontact.com/gb/products/0804287>



Classifications

ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

ESL 60X10 - Insert strip



0804287
<https://www.phoenixcontact.com/gb/products/0804287>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk