

## HPP V4 Power crimp contact male 1,5mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 500 0401
Specification	HPP V4 Power crimp contact male 1,5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09465000401">https://b2b.harting.com/09465000401</a>

### Identification

Category	Contacts
Series	HARTING PushPull (V4)
Type of contact	Crimp contact

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	1.5 mm <sup>2</sup>
Conductor cross-section	AWG 16 ... AWG 14

### Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

## Commercial data

Packaging size	100
Net weight	0.46 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors