

Datasheet

RS Pro Test Lead Kit, CAT III 1000 V

RS Stock No: **243-2998**



FEATURE:

Probe

- Standard: EN 61010-031
- Maximum rated voltage to earth and measuring category
With push-on caps: CAT IV 600V, CAT III 1000V
- Without push-on caps: CAT II 1000V
- Maximum rated current: 10 A
- Comfort-grip, safety-shrouded, right-angle plug
- UL recognized, double insulated wire: Length: 48"(1.2m), AWG: 18

Alligator

- Standard: EN 61010-031
- Maximum rated voltage to earth and measuring category: CAT III 1000V
- Maximum rated current: 10 A
- Slip-on insulated alligator clips for use with test leads probe