



## Catalogue No 666 & 667 Feeler Leaf

### Specification

Accuracy to U.S.A. Fed. Spec GGG-G-17C

<b>ENGLISH</b>			
Cat. No.		666	667
Leaf Length		25'/20'	12'
Leaf Type		Straight	Straight
No. of Leaves		Roll	-
Nominal Size (inch)	Thickness Tolerance (inch) U.S.A. Fed. Spec GGG-G-17C		
0.001	+/- 0.00016	x	x
0.0015	+/- 0.00016	x	x
0.002	+/- 0.0002	x	x
0.0025	"	x	x
0.003	"	x	x
0.004	"	x	x
0.005	"	x	x
0.006	"	x	x
0.007	"	x	x
0.008	+/- 0.0024	x	x
0.009	"	x	x
0.010	0.00035	x	x
0.011	"	x	x
0.012	"	x	x
0.013	+/-0.00043	x	x
0.014	"	x	x
0.015	"	x	x
0.016	+/- 0.00047	x	x
0.017	"	x	x
0.018	"	x	x
0.019	+/- 0.00055	x	x
0.020	"	x	x
0.021	"	x	x
0.022	"	x	x
0.023	"	x	x
0.024	"	x	x
0.025	+/- 0.00067	x	x
0.026	"		x
0.027	"		x
0.028	"		x
0.029	"		x
0.030	"		x

