



DCF610D2

10.8V XR Li-Ion Screwdriver - 2.0Ah

Selling Proposition

- Powerful 10.8V Screwdriver for screwdriving & drilling applications
- Compact, lightweight design
- 15 Position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
- 3 LED 'Halo' ring provides maximum illumination to work piece
- Parabolic switch profile allowing for greater control over speed of application
- Ergonomic handle and rubber overmold to provide ultimate end user comfort

Standard Equipment

- 2 x 2.0Ah XR Li-Ion battery packs
- Multi-voltage XR charger
- Heavy duty kit box

Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	10.8 V
Battery Capacity	2.0 Ah
Max Torque	8 Nm
Power Output	154 Watt
No Load Speed	0-1050 rpm
Bit Holder	6.35mm
Weight	0.96 kg