

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Facilitates easy installation and secure positioning.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under dynamic conditions.
- **Static Load Rating of 50 N/mm²:** Supports high static loads for robust applications.
- **Bore Size of 15.02 mm:** Suitable for a variety of shaft sizes.
- **Outside Diameter of 21.05 mm:** Fits standard housing dimensions.
- **Width of 10 mm:** Compact design for space-constrained environments.

RS PRO Flanged Plain Bearing, Sintered Bronze

RS Stock No: 529-032



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from high-quality sintered bronze, it offers excellent durability and performance under varying load conditions. Ideal for use in machinery where space is limited, this bearing ensures smooth operation and longevity.

General Specifications

Bore Size	15.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	21.05 mm
Width	10 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

