

## Technical data sheet

Article number:  
251-21309

**G51NC**



<b>Product Group</b>	Edge protection for cut-out sections
<b>Product Family</b>	Flexiform G51N PA6 grommet strip
<b>Material</b>	Polyamide 6 (PA6)
<b>Colour</b>	Natural (NA)
<b>Flammability</b>	UL 94 HB
<b>Height (H)</b>	4.3 mm
<b>Height (H2)</b>	2.7 mm
<b>Operating Temperature</b>	-60 °C to +95 °C
<b>Package Content</b>	25 m
<b>Package Content packed in</b>	pack
<b>Panel Thickness max.</b>	3.3 mm
<b>Panel Thickness min.</b>	2.1 mm
<b>Specifications</b>	NASM21266
<b>Width (W)</b>	5.7 mm
<b>Width (W2)</b>	3.5 mm

HF ✓ RoHS ✓

**NASM**