

# WXT103N

## Weathersafe Extreme Single Gang 13A Fused Spur

### Features & Benefits

- Weathersafe 'Extreme' impact resistant solid ribbed lid
- Fitted with 13A fuse link
- Power 'ON' neon indicator showing switch status
- Easy release lid catch
- Multiple M20 threaded screw-outs
- Lockable cover facility
- Complies with BS1363
- IP66 weatherproof rating



### Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class I
Operating Temperature	-5°C to 55°C
Ingress Protection Rating	IP66
Switch type	Double Pole Switch
Mounting Hole Centres (mm)	120 (Top/Bottom), 72 (Left/Right)
Cable Entry(s)	Back Entry, (Multiple M20 Threaded Screw-Outs Top/Bottom/Sides)

# Data sheet

## WXT103N

Safety / Weathersafe Extreme

### General

Weight (g)	363
Height (mm)	148
Width (mm)	108
Depth (mm)	75.5
Body Construction	Polycarbonate (Impact Resistant)
Product Colour	Grey
Accessories (Included)	x2 Cable Glands
EAN Number	5012483012741
Guarantee Period	3 Years

### Line Diagrams

