


# NOZZLES


FOR WHA900 AND WHA3000P

HOT AIR STATIONS




**ROUND (NO VACUUM)**

Cat No.	A		B	
	IN.	MM	IN.	MM
0058736881	0.098	2.50	--	--
0058736867	0.157	4.00	--	--
0058736870	0.276	7.00	--	--
0058736836Δ	0.453	11.50	--	--




**ROUND BENT (NO VACUUM)**

Cat No.	A		B	
	IN.	MM	IN.	MM
0058736882	0.059	1.50	--	--




**ROUND DUAL (NO VACUUM)**

Cat No.	A		B	
	IN.	MM	IN.	MM
0058736883	0.098	2.50	0.374	9.50




**2-SIDES HEATED**

Cat No.	A		B	
	IN.	MM	IN.	MM
0058736840	0.583	4.80	0.846	21.50
0058736842	0.394	10.00	0.551	14.00
0058736843	0.421	10.70	0.421	10.70
0058736841	0.472	12.00	0.748	19.00
0058736876Δ	0.472	12.00	1.063	27.00
0058736857Δ	1.496	38.00	1.496	38.00
0058736873Δ	1.575	40.00	1.575	40.00



**4-SIDES HEATED**

Cat No.	A		B	
	IN.	MM	IN.	MM
0058736839	0.433	11.00	0.433	11.00
0058736818	0.583	14.80	0.583	14.80
0058736814	0.709	18.00	0.709	18.00
0058736807	0.807	20.50	0.807	20.50
0058736804	1.024	26.00	1.024	26.00
0058736833	1.260	32.00	1.260	32.00
0058736891	1.417	36.00	1.417	36.00
0058736890Δ	1.693	43.00	1.693	43.00
0058736838	0.394	10.00	0.571	14.50
0058736880Δ	0.472	12.00	0.945	24.00
0058736837	0.512	13.00	0.610	15.50
0058736892Δ	0.551	14.00	1.063	27.00
0058750721	0.669	17.00	0.925	23.50
0058736877Δ	0.669	17.00	1.142	29.00
0058736998Δ	0.906	23.00	1.398	35.50
0058736999Δ	1.201	30.50	1.909	48.50
0058736858Δ	1.260	32.00	1.732	44.00
0058750709Δ	1.496	38.00	1.909	48.50
0058750714Δ	1.496	38.00	2.402	61.00



**ROUND DUAL (NO VACUUM)**

Cat No.	A		B	
	IN.	MM	IN.	MM
0058736883	--	--	--	--

## CSF REPLACEMENT RUBBER INSERTS

Cat. No.	Description
W58713798	Small, 3 mm
W58713799	Large, 6 mm

(Δ) Denotes Make To Order. Contact us for a quote and lead-time.



# Weller®

www.cooperhandtools.com/weller