

## 19 L 24

### Socket 1/2"

hexagon UD-profile, long pattern

Code	ETIM
<b>2300575</b>	<b>EC002203</b>
EAN	UNSPSC
<b>4010886896242</b>	<b>27-11-17-04</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-02-18</b>
Customs tariff number	
<b>82042000</b>	



### Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

### Article information

Contents (Qty of pieces)	1	Standard	DIN 3124 ISO 2725-1 DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,257 kg	Width across flats l [mm]	24
Total length [mm]	82 mm	Backup	Ball Catching Cricket
Total width [mm]	33 mm	Insert-Ø1	33,0 mm
Surface	polished, chrome-plated	Working length	82,0 mm
Material	Chrome-vanadium steel	Insert-Ø2	29,0 mm
Drive connector square female (metric)	12,5 mm	Operating depth	26,0 mm
Drive connector square female [inch]	1/2"		