

DGF Series - Large industrial type - Rubber hose

Fixed bracket
 Inlet: G 3/8 F
 Inlet for DGF 1310: G 1/2 M
 Pressure: 12 bar
 Temperature: -15°C to +40°C



	A (mm)	B (mm)	ID/OD (mm)	Length (m)	Coupler	Flow rate (l/min)	Swivel inlet (BSPP)	Weight (kg)	Parts Numbers
	520	462	8 x 14	10	BSI 06	500	G 3/8 F	17	DGF 0810BS
	520	462	8 x 14	15	BSI 06	350	G 3/8 F	18.5	DGF 0815BS
	520	462	8 x 14	20	BSI 06	260	G 3/8 F	20	DGF 0820BS
	520	462	8 x 14	10	ESI 07	500	G 3/8 F	17	DGF 0810ES
	520	462	8 x 14	15	ESI 07	350	G 3/8 F	18.5	DGF 0815ES
	520	462	8 x 14	20	ESI 07	260	G 3/8 F	20	DGF 0820ES
	520	462	10 x 17	10	ESI 07	900	G 3/8 F	18	DGF 1010ES
	520	462	10 x 17	15	ESI 07	700	G 3/8 F	19	DGF 1015ES
	540	462	13 x 20	10	ESI 07	1800	G 1/2 M	19	DGF 1310ES
	520	462	8 x 14	10	ISI 06	500	G 3/8 F	17	DGF 0810IS
	520	462	8 x 14	15	ISI 06	350	G 3/8 F	18.5	DGF 0815IS
	520	462	8 x 14	20	ISI 06	260	G 3/8 F	20	DGF 0820IS
	520	462	10 x 17	10	ISI 06	833	G 3/8 F	18	DGF 1010IS
	520	462	10 x 17	15	ISI 06	700	G 3/8 F	19	DGF 1015IS
	520	462	13 x 20	10	ISI 08	1800	G 1/2M	19	DGF 1310IS
	520	462	8 x 14	10	CSI 06	500	G 3/8 F	17	DGF 0810CS
	520	462	8 x 14	15	CSI 06	350	G 3/8 F	18.5	DGF 0815CS
	520	462	8 x 14	20	CSI 06	250	G 3/8 F	20	DGF 0820CS
	520	462	10 x 17	10	CSI 06	833	G 3/8 F	18	DGF 1010CS
	520	462	10 x 17	15	CSI 06	700	G 3/8 F	19	DGF 1015CS
	520	462	13 x 20	10	CSI 08	1800	G 1/2 M	19	DGF 1310CS

