

Perfection V39



Capture, store and share your images and documents quickly and easily with this stylish new compact scanner for the home and office

This easy-to-use, USB-powered scanner has a new sleek and space-saving design. An integrated stand allows for added flexibility as the scanner can be used flat as well as on its side to help save desk space. With 4800dpi and fast scan speeds, the V39 will produce high-quality results quickly. You can easily store and share your photos and documents online by scanning to cloud or straight to Facebook and Picasa.

Ultra-compact and tidy

The V39's power and connectivity is handled via a single Micro USB to reduce cable clutter and keep your workspace tidy. The device also has a built-in stand for flexible scanning to suit your desk space.

Fast, high-quality results

Thanks to Epson's ReadyScan LED Technology, you can start scanning instantly - no warm-up time is required. Make sure that even your old photos look their best with Epson Easy Photo Fix software, which improves the quality of your scans by removing dust, restoring faded colours and correcting backlight. Even your scanned documents will look great as the V39 comes with a range of enhancement features, enabling you to improve text sharpness and remove unwanted 'bleed-through' from double-sided documents.

Convenient

To make scanning quick and easy, the V39 has four one-touch buttons so you can scan, copy, share and turn your photos and documents into multi-page searchable PDFs¹ at the push of a button. For added versatility, a fully-detachable lid makes scanning of thick books, photo albums and other bound items possible. Thanks to clever software the V39 can even handle larger photos and documents - simply scan the large item in A4 sections and then seamlessly join the sections back together to create the whole image¹. Scan directly to cloud storage services such as SugarSync and Evernote and easily share your photos with family and friends by scanning straight to Facebook and Picasa.

DATASHEET / BROCHURE



KEY FEATURES

- **High resolution 4800dpi scanning**
Produce high-quality photo and document scans
- **Power and connectivity via Micro USB**
No need for mains powered ac adapter or separate power cable
- **Integrated stand for upright scanning**
Save space on your desk or counter top
- **Four one-touch buttons**
Quick scanning to make regular repetitive scanning tasks easier
- **Clever software**
Ensure the best quality scans and store and share your photos online

PRODUCT SPECIFICATIONS

TECHNOLOGY

Scanner Type	Flatbed Scanner
Optical Resolution	4,800 DPI x 4,800 DPI (Horizontal x Vertical)
Optical Resolution	Main 4,800 DPI
Scanning color depth	Input: 48 Bits Color , Output: 24 Bits Color

SCANNER

Optical Sensor	CIS (Contact Image Sensor)
Light Source	White LED
Scanning Method	Fixed documents and moving carriage
Output Resolution	50-6400 (1 dpi step) DPI

SCANNING FEATURES

Features	RGB colour dropout, Automatic area segmentation, Text enhancement, A2 Stitching, Scan to Cloud Storage, Scan to Selected Photo Sharing Websites, 4 push buttons (PDF, Send, Copy, Start), Integrated stand for upright scanning
Output formats	BMP, JPEG, TIFF, multi-TIFF, PDF, searchable PDF
Image Improvement	Dust removal, Backlight Correction, Colour Restoration

CONNECTIVITY

Interfaces	USB 2.0 Micro-AB
------------	------------------

GENERAL

Included Software	ArcSoft Scan-n-Stitch Deluxe (Windows only), Epson Copy Utility, Epson Document Capture (Mac only), Epson Document Capture Pro (Windows only), Epson Easy Photo Scan, Epson Scan
Sound Power	Operation: 5.4 B (A)
Product dimensions	249 x 364 x 39 mm (Width x Depth x Height)
Product weight	1.5 kg
Compatible Operating Systems	Mac OS 10.7.x, Mac OS 10.8.x, Mac OS 10.9.x, Mac OS X 10.6.8, Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP SP2 or higher
Supported Humidity	Operation 20% - 80%, Storage 20% - 80%
Supported Temperature	Operation 10° C - 35° C, Storage -20° C - 60° C

OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	B11B232401
EAN code	8715946544298
Layer	21 Units
Layer Block	28 Units

Perfection V39

WHAT'S IN THE BOX

- Driver and utilities (CD)
- Main unit
- Setup guide
- USB cable
- User manual (CD)
- Warranty document



For more information please contact:

Home users: 0343 90 37766
 Business users*: 0871 42 37766
 Republic of Ireland: 01 436 7742
 Or visit us at <https://www.epson.co.uk/contactus>
 * 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

1. - Windows only

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
 Product information is subject to change without prior notice.
 Last extracted: 2020-04-28

EPSON®