



tesa® 4298

Product Information



Medium duty tensilized non-staining strapping tape

Product Description

tesa® 4298 is a medium duty tensilized polypropylene strapping tape with a natural rubber adhesive system. It is easy to handle, and can be removed residue-free. The strapping tape is especially suitable for holding and securing applications in the appliance industry.

Product Features

- The tape adheres well on both polar and non-polar surfaces, and features a high tensile strength and a low elongation.
- tesa® 4298 is a specifically designed tape which is stain and adhesive-transfer resistant.
- It features high tack, strong adhesion, and resistance against environmental stress.

Application Fields

- tesa® 4298 is mainly used for closing, holding, and securing applications
- The tape can also be used for reinforcing
- The strapping tape is mostly used in the appliance, office equipment, and furniture industries
- The natural rubber adhesive ensures a strong hold on both polar and non-polar surfaces
- The tape can be removed residue-free

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-------------------|--------|
| • Backing | MOPP | • Total thickness | 114 µm |
| • Type of adhesive | natural rubber | • Color | blue |

Properties/Performance Values

- | | | | |
|-----------------------|----------|-----------------------------|-----|
| • Elongation at break | 35 % | • No discoloration | yes |
| • Tensile strength | 300 N/cm | • Residue-free removability | yes |

Adhesion to Values

- | | |
|---------|--------|
| • Steel | 5 N/cm |
|---------|--------|



tesa[®] 4298

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04298>