

## Technical data sheet

Article number:  
162-30500

SBPPHDR35



<b>Product Group</b>	PP High Abrasion-resistant Narrow Pitch Spiral Binding
<b>Product Family</b>	SBPPHDR
<b>Material</b>	Polypropylene (PP)
<b>Colour</b>	Black (BK)
<b>Bundle Diameter max (metric)</b>	42 mm
<b>Bundle Ø min.</b>	35 mm
<b>Flammability</b>	UL 94 HB
<b>Nominal Ø</b>	35 mm
<b>Operating Temperature</b>	-30 °C to +100 °C
<b>Package Content packed in</b>	EA
<b>Pack Cont.</b>	1 m
<b>Pitch (P)</b>	6.5 mm
<b>Wall (WT)</b>	3.5 mm

HF ✓

RoHS ✓