

BLUEMARK MAG WM-M (D30) - Magazine



0802747

<https://www.phoenixcontact.com/gb/products/0802747>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Magazine, length: 0.12 m, width: 76 mm, height: 120 mm, color: white



Your advantages

- In conjunction with the BLUEMARK CLED printer, the magazine for accommodating WMTB-AL... ensures printing with a high degree of positioning accuracy.

Commercial data

Item number	0802747
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG121Z
Product key	BG121Z
Catalog page	Page 193 (C-3-2019)
GTIN	4046356845854
Weight per piece (including packing)	56.1 g
Weight per piece (excluding packing)	58.2 g
Customs tariff number	90179000
Country of origin	DE

BLUEMARK MAG WM-M (D30) - Magazine



0802747

<https://www.phoenixcontact.com/gb/products/0802747>

Technical data

Product properties

Product type	Magazine
--------------	----------

Dimensions

Width	76 mm
Height	120 mm
Depth	4 mm
Length	120 mm

Material specifications

Color	white
Material	POM

Classifications

ECLASS

ECLASS-13.0	19140615
-------------	----------

ETIM

ETIM 9.0	EC001675
----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk