



Selection of 244 tools in foam module

CPP-244MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 ¤,-

<https://www.sam-outillage.com/>





DESCRIPTION



Selection of 244 tools in foam module

Ideal selection for HGV mechanical and maintenance jobs. Perfect for carrying out interventions on HGV and agricultural machines and equipment requiring large tools.

SPECIFIC DATA

Designation	AGRICULTURAL AND HGV KIT WITH 244 TOOLS IN FOAM MODULE
Sales reference	CPP-244MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



Weight (kg)	36.000
Guarantee	O SAM TOOL guarantee.










Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

Toolset

	x 1	Foam module 3/3 with 68 tools 1/2" and 1/4" CP-68MM
	x 17	1/2" short hexagonal sockets in mm SH-... Ref : 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 27 30 32 mm
	x 1	1/2" joint handles S-14... Ref : S-141
	x 1	1/2" site ratchet with lever reversion S-157B
	x 1	1/2" sliding locking handle S-120
	x 3	1/2" extension with locking S-...V Ref : S-205 S-208 S-215
	x 1	1/2" joint S-240
	x 5	1/2" long bi-hexagonal sockets in mm SL-...Douilles_MM Ref : 15 17 19 21 22 mm
	x 1	Site 1/4" ratchet R-157B















SAM Outillage















10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 ¤,-

<https://www.sam-outillage.com/>




	x 1	1/4" joint R-240
	x 2	Straight 1/4" extensions R-21... Ref : R-210 R-217
	x 1	Flexible 1/4" extension R-220
	x 10	Screw driving bits ph + hex E-900J10
	x 10	Screw driving bits pz +tx E-910J10
	x 10	Screw driving bits fte +txr E-920J10
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 5 6 7 8
	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 4 5 6 7 8
	x 8	One-piece screwdriver socket 1/4" for Torx® mark RT-... Ref : 9 10 15 20 25 27 30 40
	x 1	1/4" bit holder socket RD-1
	x 1	Fitted 1/4" extension R-225
	x 15	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 3,5 4 4,5 5 5,5 6 7 8 9 10 11 12 13 14 15 mm
	x 1	1/4" sliding handle R-120
	x 1	10-impact tool foam module M1-10MM Ref : M1-10MM


	x 1	Bodyworker's chisel 1-... Ref : 1B
	x 1	Punch 10 mm 8N-...A Ref : 8N-3A
	x 1	Constant section cape chisels 4-...-A Ref : 4-200-A
	x 1	SAMSOPUS® riveting hammer, three-material handle 310-...TM Ref : 310-32TM
	x 1	Mallets with interchangeable tips 320-...D Ref : 320-32D
	x 5	Long drift punches 7-...A Ref : 7-25A - - 7-35A - - 7-50A - - 7-70A - - 7-90A
	x 1	MODULOSAM® for hammers and stamping tools MOD-64
	x 1	Foam module 1/3 with 12 combination spanners 8 to 22 mm 50N-J12MM Ref : 50N-J12MM
	x 12	Extra-thin combination wrench 50N-... Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 19 - 21 - 22 mm
	x 1	MODULOSAM® for combination wrenches MOD-59 Ref : MOD-59
	x 1	Foam module 1/3 with 4 pliers, polished chrome-plate P13-J4MM Ref : P13-J4MM
	x 1	Polished chrome-plated stacked-branch multigrip pliers 209-25B Ref : 209-25B
	x 1	Vice-grip, 45 - 50 mm opening 212-22 Ref : 212-22
	x 1	Polished chrome-plated universal pliers 204-...G Ref : 204-18G




x 1


 x 1
Chrome-plated polished diagonal cutting pliers
232-...G
Ref : 232-16G


 x 1
Empty foam module 1/3 for 1 multigrip pliers + 1 vice-grip
MOD-63


 x 1
Foam module 2/3 sawing
690-J5MM
Ref : 690-J5MM


 x 1
Double tip scriber
665-1
Ref : 665-1

 x 1
Flexible rules
781-...
Ref : 781-3


 x 1
Short measures with twin-material casings
UB-...
Ref : UB-519

 x 1
Lever type SAMSOCUT® metal saw
791
Ref : 791

 x 10
Hss bi-metal opticut metal saw blades
691-...A
Ref : 691-E10A

 x 1
18 leds 180° magnetic inspection lamp
2953R
Ref : 2953R


 x 1
Electrician's cable stripper knife
370-2
Ref : 370-2


 x 1
Empty foam module 1/3 for sawing accessories
MODM-32
Ref : MODM-32































x 1

Foam module 1/3 with male keys and accessories
62-R72MM
Ref : 62-R72MM

 x 9
Rack of 9 hexagonal keys
62-R9A...
Ref : 62-R9A

 x 9
Rack of 9 Torx® male keys
66-R9A

	x 9	Rack of 9 male 6-flat keys with spherical head in mm 67-AR9A Ref : 67-AR9A
	x 9	Rack of 9 Resistorx® male keys 59-R9A Ref : 59-R9A
	x 9	Rack of 9 long 6-flat male keys 1/4" 63-R9A... Ref : 63-R9A
	x 1	Self-retracting blade knife 378-40 Ref : 378-40
	x 1	Padlock CAD-... Ref : CAD-25
	x 1	Universal hand shears 331-16 Ref : 331-16
	x 5	Set of 5 helix pullers 761-C-5 Ref : 761-c-5
	x 1	Pen light 1396-LS Ref : 1396-LS
	x 1	1/4" socket holder EVC Ref : EVC
	x 1	Satin-finish adjustable wrenches 54-C... Ref : 54-C10
	x 1	Empty foam module 1/3 for accessories MODM-11 Ref : MODM-11
	x 1	Foam module 1/3 of 5 files with handles LPJ-1MM Ref : LPJ-1MM
	x 1	Fitted flat hand file LPM-...E Ref : LPM-25ME
	x 1	Fitted half-round files LDR-...-E Ref : LDR-25-ME

	x 1	Fitted round files LR-...-E Ref : LR-20-DE
	x 1	Fitted triangular files LT-...E Ref : LT-20-ME
	x 1	Fitted square files LCA-...E Ref : LCA-20-ME
	x 1	MODULOSAM® for files and rasps MODM-33 Ref : MODM-33
	x 1	Foam module 1/3 with 6 combination spanners 50N-J6MM Ref : 50N-J6MM
	x 6	Extra-thin combination wrench 50N-... Ref : 22 - 24 - 27 - 29 - 30 - 32 mm
	x 1	Empty foam module 1/3 for large wrenches MODM-29 Ref : MODM-29
	x 1	Foam module 1/3 with 6 tools 3/4" in mm 78-C6MM Ref : 78-C6MM
	x 1	Centre reversion 3/4" ratchet C-150
	x 1	Handle for c-150 ratchet and c-140 joint handle C-125-A
	x 1	Sliding 3/4" locking handle C-120A
	x 2	3/4" extensions C-2... Ref : C-208 - C-215
	x 1	3/4" joint C-240
	x 1	Empty foam module 1/3 for accessories 3/4" MODM-14



x 1

Foam module 1/3 with 17 tools 3/4" 6-flat in mm
78-CH17MM
Ref : 78-CH17MM



x 18

3/4" short hexagonal sockets in mm
CH-...Douilles_3/4_MM
Ref : 22 23 24 26 27 29 30 32 35 36 38 41 42 46 50 54 55mm



x 1

Empty foam module 1/3 for sockets 3/4"
MODM-15

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

