



verso mobile workstand with 1 drawer cabinet. Featuring a robust, steel channel, framework with 100mm diameter castors and a 30mm lino worktop. Cabinet - WxDxH: 525x550x250mm. Drawer configuration: 1x 175mm with 100% extension slides (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 700x600x930mm.

Breite [mm]: 700
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 45.49
EAN-Code: 5039350125250
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Crimson red
Main RAL colour	RAL 3004
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	1
Drawer load capacity [kg]	50
Drawer height 1 [mm]	175

Schrank, Gehäuse, Werkbank und EAP



Worktop/housing top type

Lino