

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



PRC contact carrier without contacts, black, 5-pos., 630 V/30 A, for 1.5 mm² ... 6 mm² crimp contacts



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	4 0 4 6 3 5 6 8 6 4 3 5 0
Weight per Piece (excluding packing)	11.3 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General data

Number of positions	5
Protection class	П
Color	black
Locking type	Snap-in locking
Insertion/withdrawal cycles	50
Pull-out-force	150 N ± 50 N
Insertion force	40 N ±10 N

Connection data

Rated current	30 A (with 6 mm² conductor cross section)
Rated voltage (III/2)	690 V
Conductor cross section flexible min.	2.5 mm ²
Conductor cross section flexible max.	6 mm²
Conductor cross section solid min.	2.5 mm ²
Conductor cross section solid max.	6 mm²
Stripping length	11 mm



Technical data

Connection data

Torque	2.5 Nm ±0.1 Nm (Tightening torque nut)
Wrench size, union nut	32.00 mm
Type of contact	Male connector
Stripping length of the sheath	12 mm

Material data

Contact material	Cu
Contact surface material	silver-plated
Contact carrier material	mPPE
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27279220
eCl@ss 7.0	27440103
eCl@ss 8.0	27440102

ETIM

ETIM 4.0	EC002061
ETIM 5.0	EC002635

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals



Approvals

Approvals submitted

Approval details

UL Listed (III)	
mm²/AWG/kcmil	14-10
Nominal current IN	30 A
Nominal voltage UN	600 V

cUL Listed • • • • • • • • • • • • • • • • • • •	
mm²/AWG/kcmil	14-10
Nominal current IN	30 A
Nominal voltage UN	600 V

Accessories

Accessories

Circular connector (cable-side)

Contact - CK2,5-M-2,5 AG - 1409207



Turned 2.5 crimp contact, individual male contact, core diameter 2.5 mm², silver-plated



Accessories

Contact - CK2,5-M-4 AG - 1409208



Turned 2.5 crimp contact, individual male contact, core diameter 4.00 mm², silver-plated

Contact - CK2,5-M-6 AG - 1409209



Turned 2.5 mm crimp contact, pin single contact, conductor cross section 6 mm², silver-plated

Crimping tool

Crimping pliers with digital display - SF-Z0025 - 1607452



Crimping pliers for turned crimp contacts \varnothing 1.0 mm / \varnothing 1.6 mm / \varnothing 2 mm / \varnothing 3.6 mm, litz wire cross section of 0.08 mm² ... 6 mm²

Protective cover

Protective cap - PRC COVER M - 1409237



Protective cap for 3 and 5-pos. PRC device plugs

Screwdriver tools

Screwdriver - SZF 1-0,6X3,5 - 1204517




Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip


Drawings



Dimensional drawing




Dimensional drawing



Housing cutout

Dimensional drawing



Dimensional drawing

Schematic diagram



Connector pin assignment

Dimensional drawing

Phoenix Contact 2015 @ - all rights reserved http://www.phoenixcontact.com