






0.5 D

TYPE	A	B
B-3	70±0.5	80 ⁺¹ ₀
CHM-3	100±0.5	110 ⁺¹ ₀
DH-3	130±0.5	140 ⁺¹ ₀
FM-3	190±0.5	200 ⁺¹ ₀