



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58495-2
PROCRIMPER DIE ASSY MULTIMATE

TE Part # 91505-1
CCII TYPE III+ 24-16 ASSY

TE Part # 200893-2
INSERTION TOOL CONT

TE Part # 58495-1
PRO CRIMPER ASSY MULTIMATE





TE Part # 539972-1
EXTRACTION TOOL



TE Part # 305183
EXTRACT TOOL TYPE 2 20-16



TE Part # 2384426-2
SDE F TYPE III+ 0.56-0.12mm2 DIE SET



TE Part # 2384426-1
SDE F TYPE III+ 0.56-0.12mm2 ASSY



TE Part # 169475-1
MINI CERTI-LOK III+

Customers Also Bought



TE Part #3-106505-2
9P.HDP20 REC.ASSY.



TE Part #1558666-7
T9GS1L14-24



TE Part #1-1393231-2
RP412024



TE Part #2301838-1
AMPL REC HD20, VERT, 9P, B/L,4-40
INS



TE Part #2-1393258-0
V23047-A1036-A501



TE Part #965901-1
JPT REC 2.8 Contact SRC Sn



TE Part #2-1393236-4
V23092-A1024-A301



TE Part #164161-9
.062 PIN ASSY.3+

Documents

Product Drawings

TYPE 3+ STIFT STD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_164163-8_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_164163-8_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_164163-8_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English