



## ■ IS18

➔ Insulated slotted screwdrivers with slim fit blade

### ▶ STANDARD :

EN 60900 / IEC60900  
ISO 2380-1

### ▶ ADVANTAGES :

No extra insulation thickness on head of tool.



Ref.	Ø blade	Blade length	Weight
IS18 02 x 70	2 mm	70 mm (non recessed)	16 g
IS18 03 x 100	3 mm	100 mm (non recessed)	30 g
IS18 04 x 120	4 mm	120 mm	52 g
IS18 05,5 x 100	5,5 mm	100 mm	50 g
IS18 05,5 x 150	5,5 mm	150 mm	72 g
IS18 06,5 x 150	6,5 mm	150 mm	36 g
IS18 08 x 150	8 mm	150 mm	92 g
IS18 08 x 200	8 mm	200 mm	142 g
IS18 10 x 150	10 mm	150 mm	166 g
IS18 10 x 250	10 mm	250 mm	282 g
IS18 12 x 200	12 mm	200 mm	318 g

Document not contractually binding, errors and omissions excepted.