



## PRODUCT-DETAILS

**SP32/PG29/M****STR SWL NPB FITTING PG29 32MM-MET****General Information**

Extended Product Type	SP32/PG29/M
Product ID	7TCA296020R0262
EAN	5020963006197
Catalog Description	STR SWL NPB FITTING PG29 32MM-MET
Long Description	Nickel Plated Brass Straight Fitting with External PG29 Thread.

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

**Ordering**

EAN	5020963006197
UPC	786210275796

---

**Technical**


---

Number of Batteries	0
Color	Metallic
Material	Brass
Size	NC 32mm

---



---

**Environmental**


---

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---



---

**Container Information**


---

Package Level 1 Units	2 piece
Package Level 1 EAN	5020963006197
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

---



---

**Certificates and Declarations**


---

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

**External Classifications and Standards**


---

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

---



---

**Categories**


---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

