



ENGLISH

Datasheet

RS Pro Glass Cloth Tape Class H

RS Stock No: 134-7340



Product Description

A single-sided woven glass, cloth tape with a silicone adhesive.

Features

- Extremely high temperature resistance.
- High mechanical strength.
- Flame retardant to UL 510.
- Excellent resistance to acids and oils.

NOTE

Except where indicated otherwise, the figures stated are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24hours may be required for this to take place.

Technical Details

Typical Values

Thickness	0.18mm
Breaking Load	280 N/cm
Elongation	5%
Adhesion to steel	3.0 N/cm
Breakdown Voltage	2.5 kV
RoHS Compliant	Yes
Service Temperature	0°C to +180°C
Application Temperature	+10°C to +40°C