



Part Number : [1300830232](#)
Product Description : Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 15.24m (50.0') Cord Length
Series Number : 130083
Status : Active
Product Category : Electrical Reels
Engineering Number : 92433



Documents & Resources

Drawings
[1300830232_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Electrical Reels
Series	130083
Description	Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 15.24m (50.0') Cord Length
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678879242

Agency

CSA	LR29921
UL	E22769

Electrical

Current - Maximum per Contact	18.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Cord Type	12/3 SOW

Depth	0.34m (13.50")
Drum Lock	Ratchet
Duty	Industrial
Guide Arm	5° increments over 270° Arc
Height	0.37m (14.50")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Net Weight	22679.618/g
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Width	244.35mm (9.620")
Wire Size (AWG)	12