
ASSEMtech Europe Ltd

PRODUCT DATA SHEET



SPECIFICATION

CONTACT FORM/STYLE		A/Open	
SWITCHING VOLTAGE	Max. Vac	240	
SWITCHING CURRENT	Max. A	0.5	
SWITCHING CAPACITY (RESISTIVE)	Max. VA	10	
CONTACT RESISTANCE	Max. m Ω	100	
SWITCHING DISTANCE	Min. mm	8.0	
OPERATING TEMPERATURE	Deg. °C	-20° + 70°	
STORAGE TEMPERATURE	Deg. °C	-25° + 70°	
CASE MATERIAL		Black Polypropylene	

RECTANGULAR MAGNETIC PROXIMITY SWITCHES

PART NUMBER **\$1366**

Rev. No.	Revision Note	Date	Signature
А	FIRST ISSUE	10.6.47	P.P.



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.

BS5750/ISO 9000 Reg. No. FM 21080