

Screw connection - WP-GA HF IP66 M16 BK - 3240925

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland, metric thread, IP66 protection, angled

The figure shows the WP-GA HF IP66 M10 BK version



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710329
Weight per Piece (excluding packing)	7.2 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	36.5 mm
Height	36 mm
Width (a)	20 mm
Diameter	20.00 mm
Outside diameter	13.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

General

Color	black
Type	Angled
	Outer thread

Screw connection - WP-GA HF IP66 M16 BK - 3240925

Technical data

General

Components	free from silicone, halogen, and cadmium
Inflammability class according to UL 94	HB
Material	PA

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung / LR


Ex Approvals


Approvals submitted

Approval details

Screw connection - WP-GA HF IP66 M16 BK - 3240925

Approvals

UL Recognized 

VDE Zeichengenehmigung 

LR

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 15,8 BK - 3240682



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 15,8 BK - 3240840



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Mounting material

Protective hose fixing bracket - WP-BASE A M16 - 3241083



Fixing bracket for protective sleeves, fixed with two screws