

**KEMET Part Number: SSHB21H-04610**  
(UALSB204610000)

KEMET, SSHB21H, AC Line Filters, Dual Mode, 0.061 H



| Dimensions |                |
|------------|----------------|
| L          | 26mm MAX       |
| T          | 23mm MAX       |
| H          | 15.5mm MAX     |
| LL         | 3.5mm +/-0.5mm |
| S          | 21mm +/-0.5mm  |

| Packaging Specifications |      |
|--------------------------|------|
| Packaging:               | Tray |
| Packaging Quantity:      | 360  |
| Weight:                  | 14 g |

| General Information |                                |
|---------------------|--------------------------------|
| Series:             | SSHB21H                        |
| Style:              | Through-Hole                   |
| RoHS:               | Yes                            |
| Notes:              | Marking: 04 Lot No.            |
| Miscellaneous:      | Temperature Rise Maximum: 45 K |

| Specifications     |                |
|--------------------|----------------|
| Voltage AC:        | 250 VAC        |
| Inductance:        | 61 mH (10 kHz) |
| Current:           | 400 mA         |
| Temperature Range: | -25/+130°C     |
| DC Resistance:     | 2.25 Ohms      |