

182.72.104.66NU2..-EZylinderrollenlager

Cylindrical roller bearings

NU210-E-XL-TVP2 (Series NU2..-E)

main dimensions to DIN 5412-1, non-locating bearing,
separable, with cage

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system

(https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	50 mm
D	90 mm
B	20 mm
D ₁	78,3 mm
D _a max	83 mm
d _a max	58 mm
d _a min	57 mm
d _b min	62 mm
E	81,5 mm
F	59,5 mm
r ₁ min	1,1 mm
r _{a1} max	1 mm
r _a max	1 mm
r _{min}	1,1 mm
s	1,3 mm Axial displacement facility from central position
m	0,487 kg Mass
C _r	75000 N Basic dynamic load rating, radial

Cor	69000 N	Basic static load rating, radial
nc	9700 1/min	Limiting speed
nb	6600 1/min	Reference speed
Cur	8800 N	Fatigue limit load, radial



