

Technical data sheet

Article number:
162-30200

SBPPHDR20



Product Group	PP High Abrasion-resistant Narrow Pitch Spiral Binding
Product Family	SBPPHDR
Material	Polypropylene (PP)
Colour	Black (BK)
Bundle Diameter max (metric)	25 mm
Bundle Ø min.	20 mm
Flammability	UL 94 HB
Nominal Ø	20 mm
Operating Temperature	-30 °C to +100 °C
Package Content packed in	EA
Pack Cont.	1 m
Pitch (P)	5.5 mm
Wall (WT)	2.5 mm

HF ✓

RoHS ✓