

**Coupling**  
**EAMD-56-56-32-23X27-U**  
Part number: 8196718

**FESTO**



 [General operating condition](#)

**Data sheet**

| Feature                | Value                 |
|------------------------|-----------------------|
| Mounting diameter 1    | 32 mm                 |
| Mounting diameter 2    | 23 mm                 |
| Size                   | 56                    |
| Nominal length         | 56 mm                 |
| Mounting position      | Any                   |
| Max. rotational speed  | 5500 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C ... 60 °C      |
| Relative air humidity  | 0 - 95%               |
| Ambient temperature    | -25 °C ... 60 °C      |
| Mass moment of inertia | 172 kgmm <sup>2</sup> |
| Transmittable torque   | 73 Nm                 |
| Product weight         | 435 g                 |
| Note on materials      | RoHS compliant        |