



ENGLISH

Datasheet

Model 9139132



Specifications:

Electrical Rating	16A 250V
Dielectric Strength	1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts
Operating Temperature	-20 ~ +80°C (-4 ~ 176°F)
Degree of Protection	IP20/NEMA 1

Features:

- **CE/NF Certified**
- **Trailing socket NF 10m 1.5mm,389C green cable**
- **10meter,H05VV-F,3G1.5MM cable**