

DCH253M2-QW

18V XR SDS PLUS 24mm Hammer Drill - 2 X 4Ah



5035048439104

Product Description :

The DCH253M2 20V Max* SDS 3 Mode Rotary Hammer Kit is a high-performance drill powered by 2.1 joules of impact energy that protects professionals with reduced vibration felt at the handles using the Active Vibration Control® technology.



Product Features and Benefits :

- Bright white LED with delay feature improves visibility
- Fatigue and maximizes operating periods
- 4Ah 18V XR battery, delivers high performance, long life and maximum run time
- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 24mm
- Best in class vibration, 6.6m/s² reduces user fatigue and maximises operating periods
- Rotation stop mode for light chiseling in plaster, tiles and render and impact stop mode for rotary only drilling in wood and metal
- Brushed motor for optimum performance and power

Technical specifications :

- Max. Drilling Capacity (Wood) [Metric] : 26 mm
- Battery Capacity : 4 Ah
- Weight (Including Battery) [Metric] : 3.1 Kg
- Max. Drilling Capacity (Metal) [Metric] : 13 mm
- Vibration Measurement (Chiseling) : 5.4 m/s²
- Vibration Measurement (Drilling) : 6.6 m/s²

Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

Included items :

- Heavy Duty Kitbox (x1)
- Multi-Position Side Handle (x1)
- 4.0Ah XR Battery Pack With State of Charge Indicator (x2)
- Multi-Voltage XR Charger (x1)

DCH253M2-QW

18V XR SDS PLUS 24mm Hammer Drill - 2 X 4Ah

5035048439104



Product from the series DCH253M2

Ref	▲▼	Titre	▲▼
DCH253M2-GB		18V XR SDS-Plus Hammer Drill (2 X 4 Ah) (24 mm)	
DCH253M2-QW		18V XR SDS PLUS 24mm Hammer Drill - 2 X 4Ah	