




**Part Number :** 507528400

**Product Description :** 2.50mm Pitch, Mini-Lock  
Female Crimp Terminal, Matte Tin Plating, 26-24 AWG,  
Reel



**Series Number :** 50752

**Status :** Active

**Product Category :** Crimp Terminals

---

## Documents & Resources

### Drawings

507528400\_sd.pdf

### 3D Models and Design Files

507528400\_stp.zip

### Specifications

507529200-SPK-200.pdf

511630000-PS-000.pdf

511631000-PS-000.pdf

### Tooling Specifications

507520000-CS-000.pdf

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	50752
Description	2.50mm Pitch, Mini-Lock Female Crimp Terminal, Matte Tin Plating, 26-24 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	Mini-Lock
UPC	191128816724

#### Electrical

Current - Maximum per Contact	3.5A
Voltage - Maximum	250V AC (RMS)/DC

#### Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	61.660/mg
Packaging Type	Reel

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.28-1.42mm
Wire Size (AWG)	24, 26
Wire Size mm <sup>2</sup>	N/A

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Mini-Lock Single Row Receptacle Housings	<u>51163</u>

---

## Application Tooling

### Global

Description	Part Number
Hand Crimp Tool for Mini-Lock Crimp Terminals, 26-24 AWG	<u>2002189200</u>
FineAdjust Applicator for Mini-Lock 2.5 Wire-to-Board Receptacle Terminals, 26-24 AWG	<u>2037026700</u>
Extraction Tool for 2.50mm Pitch Mini-Lock Wire-to-Board Female Terminal	<u>638248400</u>

### Japan

Description	Part Number
S-1 Applicator for 2.50mm Pitch Mini-Lock Wire-to-Board Crimp Terminals, 26-24 AWG	<u>2069623710</u>