

LONG LIFE CUTTING METAL-EMBEDDED WOOD

EXPERT Wood with Metal Demolition Blades

EXPERT

- 1 Exceptional durability is built in with Bosch Carbide Technology
- 2 Tapered tip reaches deeper into tight spaces
- 3 Thick gauge blade offers extra robustness and stability
- 4 Reinforced teeth withstand the extreme abuse of demolition work
- 5 Progressive tooth pitch to cut material of every thickness



* vs. Bosch S1122VF



BOSCH

EXPERT WOOD WITH METAL DEMOLITION S1167XHM BLADE



- ▶ Ideal for all-round demolition use, including the toughest jobs such as cutting thick roof beams fixed with nail plate on a building renovation site; or cutting through mixed materials with hard nails and screws
- ▶ Best for demolition workers: long lasting and versatile
- ▶ Lasts up to 50x longer than Bosch S1122VF blade in tough materials
- ▶ Fits all S-shank reciprocating saws



PRODUCT PROPERTIES						ORDERING INFORMATION				
Tooth spacing [mm]	Tooth pitch [TPI]	Dimensions LxWxT [mm]	Blade material abbreviation	Max. cut capacity [mm]	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
3.5-5.0	5-7	225 x 25 x 1.25	CT	175	C1c	1	1	534 886	2 608 900 398	
3.5-5.0	5-7	225 x 25 x 1.25	CT	175	C1c	3	1	534 893	2 608 900 399	
3.5-5.0	5-7	225 x 25 x 1.25	CT	175	P1h	10	1	534 909	2 608 900 400	



BOSCH