

WATER SEPARATOR

MSC - Cyclone water separator with float drain



Part number	Female thread	Flow rate at 7 bars bar (l/min) ($\Delta P = 0,08$ Bar bar)	Temperature min/max (°C)	Max. operating pressure (bar)
MSC 100	G1/2	100 m3/h	1,5 °C / 80 °C	20,0 Bar
MSC 200	G3/4	200 m3/h	1,5 °C / 80 °C	20,0 Bar
MSC 300	G 1	300 m3/h	1,5 °C / 80 °C	20,0 Bar
MSC 600	G 1 1/2	600 m3/h	1,5 °C / 80 °C	20,0 Bar
MSC 1200	G 2	1.200 m3/h	1,5 °C / 80 °C	20,0 Bar



Part number	Dim. A (mm)	Dim. B (mm)	Dim. C (mm)	Dim. D (mm)
MSC 100	103,00 mm	257,50 mm	236,00 mm	210,00 mm
MSC 200	123,00 mm	304,00 mm	277,00 mm	285,00 mm
MSC 300	123,00 mm	304,00 mm	277,00 mm	380,00 mm
MSC 600	123,00 mm	320,00 mm	485,00 mm	560,00 mm
MSC 1200	160,00 mm	484,00 mm	443,00 mm	560,00 mm