



ENGLISH

Datasheet

RS Pro Steel Flexible Rule Imperial or Metric 300mm With UKAS Calibration

RS Stock No: **121-8208**



Product Details

RS Pro steel flexible rule of 300 mm, has high-quality British steel construction with non-glare black chrome finish. The rigid rules are metric and imperial with a high degree of accuracy. It is suitable for professionals, engineers or where a high degree of measurement accuracy. This steel rule comes with UKAS Calibration.

Features and Benefits

- Professional quality steel rules
- Comes in non-glare satin chrome finish
- Manufactured from high quality British steel
- Fully hardened and tempered
- Available in 2 lengths

**Specifications:**

Calibrated	UKAS
Finish	Black Chrome
Flexible	Yes
Folding	No
Imperial or Metric	Both
Length	300 mm
Material	Steel
Width	12.5 mm
End Style	D End
Rule Markings	Obverse Side: 16ths; 32nds; 64ths; 10ths; 20ths; 50ths; 100ths, Reverse Side: 1; 0.5 mm
Standards Met	EEC Class 1, Ref 73/362/EEC
Style	64RF
Thickness	0.5 mm