

Datasheet

RS Pro Steel Alloy Compression Spring, 98mm x 18mm, 3.19N/mm

RS Stock No: **121-270**



Product Details

RS Pro stainless steel alloy compression spring measures 98 x 18 mm and has a spring rate of 3.19 N/mm. It handles a load of 198.09 N at a minimum working length of 35.9 mm. This spring features right hand helix construction.

Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



Specifications:

Ends	Closed (Square)/Ground
Material	Steel Alloy
Free Length	98 mm
Load at Minimum Working Length	198.09 N
Minimum Working Length	35.9 mm
Outside Diameter	18 mm
Spring Rate	3.19 N/mm
Wire Diameter	2 mm