

Autodry Slimline Hand Dryer

When we say **SLIM**, we mean **ULTRA SLIM**! Our Autodry Slimline range of hand dryers project only 100mm (4 inches) from the wall, perfect for confined spaces.



Available in White Painted Steel and Brushed Stainless Steel

The revolutionary **ULTRA SLIM**, **HIGH PERFORMANCE** hand dryer, perfect for confined spaces

Key Features

- Projection of only 100mm (4") from the wall
- Automatic infrared, no touch control system
- Sleek and stylish design suitable for confined spaces
- Surface mounted
- Air velocity 30.5m/s @ 4 inches
- Reduced noise level of only 71dBA
- Hands dried in under 15 seconds
- 90 Seconds auto shut off
- Sensor range of 100mm vertically under outlet
- 2 Year guarantee
- CE certified

Technical Specification

- Operating voltage 220-240Vac, 50 – 60 HZ
- Output of 1700 watts
- IP 21
- Net weight 5.4 kg

Dimensions

- 350(w) x 345(h) x 100(d) mm



Projecting only 100mm (4 inches) from the wall, Autodry Slimline hand dryers and not just slim, they are **ULTRA SLIM** – perfect for confined spaces.

| Product Reference | Finish | Model | Cat. No |
|-------------------|---------------|-------|----------|
| Autodry Slimline | Brushed Steel | AS1 | 56762301 |
| Autodry Slimline | White | AS1W | 56762401 |