




PCB LAYOUT
(CONNECTOR TOP VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS

PANEL CUT OUT

RJXS8FP15HPE

- SERIES PREFIX
- CONTACT LAYOUT (RJ45 STYLE)
- GENDER
- THERMOPLASTIC 2.5mm to 3.8mm WITH CAP
- TRANSMISSION CLASS (CAT5e)
- HORIZONTAL MOUNT (PCB THRU HOLE)
- POTTED
- WITH EMI/RFI SHIELD

RECOMMEND MINIMUM MOUNTING PITCH

2.5-3.8mm RECOMMEND
PANEL THICKNESS



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:			THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER			Amphenol		Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR		ANGULAR	MATERIAL:		DRN: J.W	DATE: 24/12/2024	TITLE: XLNet, HORZ, IP65, POTTED, SHIELDED, W/CAP, PANEL THICKNESS 2.5-3.8		PART No: RJXS8FP15HPE
X ±10 X.X ±5 X.XX ±1		X° ±1 X°X' ±30' X°XX" ±15'	SEE COMPONENTS		CKD: P.M.	DATE: 24/12/2024			
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS			FINISH: SEE COMPONENTS		APP'D: P.M.	DATE: 24/12/2024	DRAWING No. 55011538-000-1		SHEET 2/2
DO NOT SCALE			DIMENSIONS IN MILLIMETRES		SCALE: NTS	SIZE: A3			