

M18 CCS66

M18 FUEL™ circular saw

Features

- Milwaukee® designed and built brushless POWERSTATE™ motor for up to 3x longer motor life and up to 2x more cuts per charge
 - Integrated dust blower keeps cut line clear
 - Hang hook allows safe storage of the tool
 - Integrated battery fuel gauge & LED light
 - Flexible battery system: works with all Milwaukee® M18™ batteries
 - REDLINK PLUS™ intelligence system delivers the most advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load
 - REDLITHIUM-ION™ battery pack delivers up to 2.5x more run time, up to 20% more power, up to 2x more battery life and operates better down to -20°C than other lithium-ion technologies
 - Individual battery cell monitoring optimises tool run time and ensures long term pack durability
 - 190 mm blade which gives a 66 mm depth of cut enables the saw to cut three stacked OSB boards
-
- The saw blade is mounted on the right of the saw keeping the extracted dust away from the user
 - 50° bevel capacity
 - Magnesium upper and lower guards provide best in class durability for impact resistance
 - Magnesium shoe reduces weight and maximises durability





Nothing but **HEAVY DUTY.**

RANGE SPEC (1)	M18 CCS66-0	M18 CCS66-502X	M18 CCS66-402C
Article Number	4933447255	-	4933447270
Battery pack capacity (Ah)	-	5.0	4.0
Battery type	Li-ion	Li-ion	Li-ion
Blade diameter (mm)	190	190	190
Bore size (mm)	30	30	30
By technology new	Fuel	Fuel	Fuel
Charger supplied	-	59 min	80 min
Max. cutting depth 45° (mm)	48	48	48
Max. cutting depth 90° (mm)	66	66	66
No load speed (rpm)	5000	5000	5000
No. of batteries supplied	0	2	2
Sound power level (dB(A))	94.2	-	94.2
Sound power level uncertainty (dB(A))	3	3	3
Sound pressure level (dB(A))	83.2	83.2	83.2
Sound pressure level uncertainty (dB(A))	1.5	1.5	1.5
Supplied in	-	HD Box	Kitbox
Vibration sawing of wood [ms ²]	2.0	2.0	2.0
Vibration sawing of wood uncertainty [ms ²]	1.5	1.5	1.5
Voltage (V)	18	18	18
Weight with battery pack (kg)	-	4.2	4.2
Sound power level (dB(A))	-	94.2	-



Nothing but **HEAVY DUTY.**[®]

RANGE SPEC (2)	M18 CCS66-502C
Article Number	4933448163
Battery pack capacity (Ah)	5.0
Battery type	Li-ion
Blade diameter (mm)	190
Bore size (mm)	30
By technology new	Fuel
Charger supplied	59 min
Max. cutting depth 45° (mm)	48
Max. cutting depth 90° (mm)	66
No load speed (rpm)	5000
No. of batteries supplied	2
Sound power level (dB(A))	94.2
Sound power level uncertainty (dB(A))	3
Sound pressure level (dB(A))	83.2
Sound pressure level uncertainty (dB(A))	1.5
Supplied in	Kitbox
Vibration sawing of wood [ms ²]	2.0
Vibration sawing of wood uncertainty [ms ²]	1.5
Voltage (V)	18
Weight with battery pack (kg)	4.2
Sound power level (dB(A))	-