

Product data sheet

Characteristics

NSYCMUMR50

Fixed subbase, square 50 mm, for SPACIAL S3CM HMI encl. RAL 7040.



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	Fixing on support
Anwendung	Multi-purpose
Nennmaße des Gehäuses	-
Mounting location	Between tube and support
Mounting support	Option of passing cables through the inside For 50 mm square tube
Range compatibility	Spacial S3CM
Device composition	Fixing elements 1 fixed base
Quantity per set	Set of 1

Complementary

Material	Moulded steel
Colour	Grey (RAL 7040)
Surface finish	Epoxy-polyester powder
Fixing mode	By screw - screw type M12 - fixed base location
Permanent permissible load	3.25 kg
Height	110 mm
Width	152 mm
Depth	152 mm
Diameter	152 mm
Net weight	3.5 kg

Packing Units

Package 1 Weight	3.5 kg
------------------	--------

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------