

# Pendant control

46-445.1818

Distribution by  
Rs-online<https://rs-online.eao.com/component/46-445.18...>

Your product:

---



## 46-445.1818 Pendant control

### FRONT

**Colour:** Grey

### MOUNTING

**Mounting cut-out:** Ø 22 mm

**Mounting type:** Panel mounting

### ELECTRICAL CHARACTERISTICS

**Rated insulation voltage  $U_i$ :**  $U_i$  300V -  $U_{imp}$  2.5KV (IEC-EN60947-1)

**Pollution degree:** 3

**Protection class:** II, according to EN / IEC 61140

### MECHANICAL CHARACTERISTICS

**Tightening torque:** 0.8 ... 1.2 Nm (7.1÷10.6 Lb-in)

**Weight:** 0.2 kg

### AMBIENT CONDITION

**IP front protection:** IP65, IP66

**IK front protection:** IK08

**Operating temperature:** - 35 °C ... + 80 °C

### CERTIFICATE

**Approbations:** CSA, UL

|                      |                                                                    |
|----------------------|--------------------------------------------------------------------|
| <b>Conformities:</b> | CE                                                                 |
| <b>REACH:</b>        | REACH compliant                                                    |
| <b>RoHS:</b>         | RoHS compliant                                                     |
| <b>Standards:</b>    | CSA C22-2, IEC EN 60204-1, IEC EN 60947-1, IEC EN 60947-5-1, UL508 |

## OTHER

|                            |                                   |
|----------------------------|-----------------------------------|
| <b>Short Description:</b>  | Pendant control                   |
| <b>Number of holes:</b>    | 1                                 |
| <b>Dimension:</b>          | 83 mm x 137 mm                    |
| <b>Housing material:</b>   | Plastic                           |
| <b>Product attributes:</b> | Suitable for outdoor applications |
| <b>Dimension drawings:</b> |                                   |

