

Product datasheet

Specifications



LoadCentre KQ - type B split metered distribution board - 125A - 12 + 8 TP ways

SEB36S24125

EAN Code: 5018934961712

Main

Range	Acti9
product name	Load centre KQ II B
Product or component type	Distribution board
Device application	Distribution
enclosure type	Split meter
Door type	Overall
Provided equipment	Enclosure Door Front cover Switch disconnecter - 125 A as incomer Multi-function meter - 2 nos. Shielded neutral bar 25 mm² Earth terminal block 25 mm² Pan assembly
Colour	Grey (RAL 7035)

Complementary

Enclosure mounting	Surface
[Ie] rated operational current	125 A at 400/415 V AC
protection device options	Miniature circuit breaker (MCB) (plug-on type) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) (plug-on type) as outgoer
Number of ways	12 ways (3P)outgoer for section 1 8 ways (3P)outgoer for section 2
Cable entry	top and bottom: knock-out side: knock-out
Height	1290 mm
Width	470 mm
Depth	139 mm

Environment

IP degree of protection	IP2x B internal conforming to BS EN 60529 IP3x external conforming to BS EN 60529
-------------------------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	54.0 cm
Package 1 Length	134.0 cm
Package 1 Weight	27.65 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	105.0 cm
Package 2 Width	107.0 cm
Package 2 Length	150.0 cm
Package 2 Weight	341.8 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	130
---	-----

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-------------------	--

SCIP Number	876e7d74-1a5d-4a7e-98d5-f97f7be1bf2a
-------------	--------------------------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

China RoHS Regulation	China RoHS declaration
-----------------------	--

Use Again

Repack and remanufacture

Take-back	No
-----------	----